

Mounting instruction

Multifit - CMF


MOUNTING



Step 01 Insert adapter ring in tube sheet ranging from 152-167 mm/5.98-6.57" diameter




Step 02 Adapter ring ensures perfect fit



Step 03 Insert Multifit cartridge in tube sheet, is easily secured by pressing it down by hand

UNMOUNTING



Step 04 Place the crowbar underneath the top cap



Step 05 Twist the crowbar and lift the cartridge

PLEASE NOTICE

- When moving the filters from storage to the dust collector make sure to protect the filter media against knocks, bumps and sharp edges.
- For storing the filters, ensure the goods are kept in a dry storage room at temperatures that do not exceed 40°C /104°F.
- Available for tube sheet sizes from 152-167mm / 6-6.60".
- Filter can be supplied with ground cable for ATEX rating and need to be connected to the dust collector accordingly.
- Follow all in place safety instructions for dust collector shut down procedures.

Revised: June 2017



NORDIC AIR FILTRATION
Member of the Hengst Group

sales@nordic-air-filtration.com
www.nordic-air-filtration.com